



TRANSFORMER BRACKET, 3- POSITION, ALUMINUM RACK STYLE with NEMA A and B LUG SPACING

By Chance

Catalog # [C12MW24AB](#)

Bracket, Transformer

Features

- Lightweight 6061-T6 aluminum
- Recommend maximum load ratings based on distance from bracket face to center of gravity of the installed equipment
- 14" = 2,500 lbs. maximum recommended per phase for 3 simultaneous loads
- 18" = 1,950 lbs. maximum recommended per phase for 3 simultaneous loads
- 22" = 1,600 lbs. maximum recommended per phase for 3 simultaneous loads
- 26" = 1,350 lbs. maximum recommended per phase for 3 simultaneous loads

General

Catalog Number	C12MW24AB
Type	Bolted Pole Mount Bracket
UPC	096359533436

Logistics

Carton Quantity	2
-----------------	---

Product Assets

[Sales Drawings - Wing Cluster Mount](#)
[Specifications - C12MW24AB](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
CH-C12MW24AB-SPEC-EN | REV 3/2025