



# TRANSFORMER BRACKET, 3- POSITION, ALUMINUM RACK STYLE with NEMA A and B LUG SPACING

By Chance  
Catalog # [C12MW30](#)



Bracket, Transformer, Wing-Rack Type.

### Features

- Lightweight 6061-T6 aluminum
- Recommend maximum load ratings based on distance from bracket face to center of gravity of the installed equipment
- 14" = 2,000 lbs. maximum recommended per phase for 3 simultaneous loads
- 18" = 1,550 lbs. maximum recommended per phase for 3 simultaneous loads
- 22" = 1,275 lbs. maximum recommended per phase for 3 simultaneous loads
- 26" = 1,075 lbs. maximum recommended per phase for 3 simultaneous loads
- For replacement bolts order six each P2160185P or one kit of six bolts, catalog number PSC2160587

### General

Catalog Number	C12MW30
EU RoHS Indicator	No
Material	6061-T6 Aluminum
Type	Bolted Pole Mount Bracket
UPC	096359525301

### Dimensions

Weight	46.81 lb
--------	----------

### Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

### Product Assets

[Catalogs - Aluminum Hardware & Apitong Wood](#)  
[Sales Drawings - Wing Cluster Mount](#)  
[Specifications - C12MW30](#)



A Hubbell brand