



TRANSFORMER BRACKET, 3-POSITION, ALUMINUM BANDED STYLE, 29in LUG SPACING for 7-3/4in to 12-1/4in DIA. POLES

By Chance
Catalog # [C15M36C](#)



Aluminum, banded style transformer bracket for mounting 3 transformers with 29" lug spacing. Includes six 5/8" x 2-1/2" square head machine bolts and nuts for mounting to transformer lugs.

Features

- Lightweight 6061-T6 aluminum
- Recommend maximum load ratings based on distance from bracket face to center of gravity of the installed equipment
- 14" = 3,200 lbs. maximum recommended per phase for 3 simultaneous loads
- 18" = 2,500 lbs. maximum recommended per phase for 3 simultaneous loads
- 22" = 2,000 lbs. maximum recommended per phase for 3 simultaneous loads
- 26" = 1,725 lbs. maximum recommended per phase for 3 simultaneous loads

General

Catalog Number	C15M36C
Material	6061-T6 Aluminum
Type	Banded Pole Mount Bracket

Dimensions

Distance From Pole	6 in
--------------------	------

Product Assets

- [Installation Manuals - Banded Aluminum Cluster Mount Installation Instructions](#)
- [Sales Drawings - Transformer Rack, Double Band](#)
- [Video - CHANCE Banded Transformer Bracket](#)



A Hubbell brand