



Capstan Hoist 3,000 lb. (Hydraulic, Reversible with Mounting Bracket)

By Chance
Catalog # [C3080940](#)

CAPSTAN -3000LB-HYD W/BAYONET-REVERSIBLE

Features

- Flow rate 8 gallons per minute and 1,000 psi
- Bolt-down Bracket included
- hydraulic foot control sold separately

General

Catalog Number	C3080940
Rope Speed at Rated Load	30' (9 m) per minute
UPC	096359015970

Dimensions

Dimensions	20.5 in x 26 in x 12.625 in
Dimensions Metric	52.1 mm x 66.0 mm x 32.1 mm



*Representative Image

Height	12.625 in
Height Metric	32.1 mm
Length	20.5 in
Length Metric	52.1 mm
Weight	100 lb
WeightMetric	45.4 kg
Width	26 in
WidthMetric	66 mm

Product Assets

- [Catalogs - Load Handling Accessories](#)
- [Catalogs - Powered Hoists](#)
- [Installation Manuals - CHANCE® Series 90 Capstan Hoist](#)
- [Specifications - C3080940](#)



A Hubbell brand