



## 1.5 Ton Ratchet Roller Chain Hoist

By CHANCE Utility  
Catalog # [C3090458](#)

Roller-style (bicycle) chain offers an alternative in two of the same load ratings from the CHANCE link-style chain hoist line.



### Features

- All working parts fully enclosed in housing
- Polished high-strength alloy steel chain
- Forged steel 360° swivelling load hooks with spring-loaded latches
- Controls automatically lock when under load
- Ratchet handle swings to either side
- Lifetime oil-impregnated bronze sleeve bearings require no additional lubrication

### General

Application - For Use On	60.0 lb., 27.2 kg
Connector	26 in, 66.0 cm
EU RoHS Indicator	No
Strength Rating - Ultimate	3000 lb
Style	Roller Chain Hoist
UPC	096359016304

### Dimensions

Dimensions	20 in x 7.87 in x 6.87 in
Height	6.87 in
Length	20 in
LengthMetric	50.8 mm
Weight	22 lb
WeightMetric	10.0 kg
Width	7.87 in

### Logistics

Pallet Quantity	28
Standard Package	1

### Product Assets

[Catalogs - Mechanical Hoists \(1100\)](#)  
[Installation Manuals - CHANCE 1.5, 3, 4.5 & 6-Ton Chain Hoist Operating and Repair Instructions \(P309-0432\)](#)  
[Literature - Tips of the Trade - Hoist Safety \(BR09004E\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
CH-C3090458-SPEC-EN | REV 8/2023