



# BOLT, MACHINE, SQ HEAD, 7/8in x 20in



By Chance  
Catalog # [C2050257](#)

Square head machine bolt for utility pole and crossarm construction. Rated for 25,400 lbs. tensile strength. Includes one assembled square nut, cone point and 6" thread length. Common industry slang reference is crossarm bolt or through bolt.

### Features

- Hot dip galvanized finish per ASTM A-153
- Manufactured in compliance with industry standard ANSI/IEEE C135.1
- RUS listed, c - Bolt, machine

Distance From Pole	N/A
Height	1.25 in
Length	21 in
Length - Threaded Area	6 in
Weight	3.43 lb
Width	1.25 in

### General

Catalog Number	C2050257
Coating	Galvanized, ASTM A-153
Material	Steel
Tensile Strength	25400 lb.
Type	Machine Bolts
UPC	096359013877

### Certifications And Compliance

RUS Listed Reference	c - Bolt, machine
----------------------	-------------------

### Logistics

Pallet Quantity	480
-----------------	-----

### Dimensions

Diameter	0.88 in
Diameter (Fraction)	7/8 in
Dimensions	21.000 in x 1.250 in x 1.250 in

### Product Assets

- [Catalogs - Communications Catalog](#)
- [Catalogs - Machine Bolts & DA Bolts](#)
- [Sales Drawings - Pole Support](#)
- [Sales Drawings - 7/8 Machine Bolt Or Crossarm Bolt](#)
- [Specifications - C2050257](#)