



3/4 Ton Ratchet Link Chain Hoist

By: CHANCE Lineman Tools & Equipment
Catalog # C3090438

Every CHANCE Chain Hoist is proof-tested and factory-operated at 150% of capacity rating. Lightweight high-strength handle and sheave housings are heat-treated aluminum.

Features

- All working parts fully enclosed in housing
- Polished high-strength alloy steel chain
- Forged steel 360° swivelling load hooks with spring-loaded latches
- Controls automatically lock when under load
- Ratchet handle swings to either side
- Lifetime oil-impregnated bronze sleeve bearings require no additional lubrication

General

Application - For Use On	65.0 lb., 29.5 kg
Connector	11 in, 27.9 cm
Strength Rating - Ultimate	1500 lb
Style	Link Chain Hoist
UPC	096359016229

Dimensions

Dimensions	20 in x 4.5 in x 4.75 in
Height	4.75 in
Length	20 in
LengthMetric	50.8 mm
Weight	15 lb
WeightMetric	6.8 kg
Width	4.5 in

Logistics

Pallet Quantity	72
Standard Package	1

Product Assets

[Catalogs - Mechanical Hoists \(1100\)](#)
[Installation Manuals - Ratchet Link Chain Hoists \(TD09232E\)](#)
[Literature - Tips of the Trade - Hoist Safety \(BR09004E\)](#)



A proud member of the Hubbell Family.