




TRANSFORMER BRACKET, 3-POSITION, ALUMINUM RACK STYLE with NEMA A LUG SPACING

By Chance
Catalog # [C3MW24](#)



Transformer Rack, Aluminum

Features

- Lightweight 6061-T6 aluminum
- Recommend maximum load ratings based on distance from bracket face to center of gravity of the installed equipment
- 14" = 625 lbs. maximum recommended per phase for 3 simultaneous loads
- 18" = 500 lbs. maximum recommended per phase for 3 simultaneous loads
- 22" = 410 lbs. maximum recommended per phase for 3 simultaneous loads
- 26" = 350 lbs. maximum recommended per phase for 3 simultaneous loads
- For replacement bolts order six each P2160185P or one kit of six bolts, catalog number PSC2160587

General

| | |
|----------------|---------------------------|
| Catalog Number | C3MW24 |
| Material | 6061-T6 Aluminum |
| Type | Bolted Pole Mount Bracket |
| UPC | 096359526179 |

Dimensions

| | |
|--------------------|-------|
| Distance From Pole | N/A |
| Weight | 26 lb |

Product Assets

[Catalogs - Aluminum Hardware & Apitong Wood](#)
[Sales Drawings - Wing Cluster Mount](#)