



15 kV, 110 kV BIL, Type C Standard Porcelain Cutout w/100A 10kAIC fuseholder

By Chance
Catalog # [C710112EDM](#)

15 kV, 110 kV BIL, Standard Type C Porcelain Cutout with a 100A, 10kAIC fuseholder, small eyebolt connector and a D-shape pole mounting bracket.



Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material

General

Bracket Type	D-shape for pole mounting
Catalog Number	C710112EDM
Description - Replacement	T710-112TM
Fuse Holder Type	Cutout

Dimensions

Weight	25.23 lb
--------	----------

Electrical Ratings

BIL	110 kV
Creep and Leakage Distance	8.7" (220mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A
Reference Voltage Limit - Minimum	Thru 14.4kV
Temperature Rise - Max. at 300A	38° C
Voltage - Maximum	15 kV
Voltage - Radio Interference	Ambient @ 9.41kV
Voltage Rating	15 kV

Logistics

Pallet Quantity	72 EA
Standard Package	1

Product Assets

- [Catalogs - Type C-Porcelain Cutouts](#)
- [Installation Manuals - Standard Cutout Installation Instructions](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Literature - HUBBELL® | CHANCE® RUS CUTOUT LISTING](#)
- [Sales Drawings - 110 KV BIL Cutout](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality Experience](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CH-C710112EDM-SPEC-EN | REV 6/2024