



27 kV, 125 kV BIL, Type C Standard Porcelain Cutout w/100A 8kAIC fuseholder

By CHANCE Utility
Catalog # [C710211E](#)

27 kV, 125 kV BIL, Standard Type C Porcelain Cutout with a 100A, 8kAIC fuseholder, small eyebolt connector and no bracket.



*Representative Image

Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material

General

Bracket Type	No Bracket
Description - Replacement Fuse Holder	T710-211T
Type	Cutout
UPC	096359029380

Dimensions

Weight	19.923 lb
--------	-----------

Electrical Ratings

BIL	125 kV
Creep and Leakage Distance	12.6" (319mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A
Reference Voltage Limit - Minimum	Thru 24.9kV
Temperature Rise - Max. at 300A	33° C
Voltage - Maximum	27 kV
Voltage - Radio Interference	Ambient @15.66kV
Voltage Rating	27 kV

Logistics

Pallet Quantity	48
Standard Package	1

Product Assets

[Catalogs - Type C-Porcelain Cutouts \(10A\)](#)
[Installation Manuals - Standard Cutout Installation Instructions](#)
[Literature - SF11036E_HPS CHANCE RUS Cutout Listing](#)
[Literature - Switching Line Card_FAQ_2019](#)
[Sales Drawings - 125KV BIL Cutout \(SA710-2\)](#)
[Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience \(VI10004E\)](#)
[Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality \(VI10005E\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-C710211E-SPEC-EN | REV 4/2023