CHANCE®

15 kV, 110 kV BIL, Type C Standard Porcelain Cutout w/100A 10kAIC fuseholder

By CHANCE Utility
Catalog # C710112PZM

15 kV, 110 kV BIL, Standard Type C Porcelain Cutout with a 100A, 10kAIC fuseholder, parallel-groove connector and no bracket.

*Representative Image

Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 – 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material

General

Bracket Type	No Bracket
Description - Replacement Fuse Holder	T710-112TM
Type	Cutout
UPC	096359406457

Dimensions

Weight	17.73 lb

Electrical Ratings

BIL	110 kV
Creep and Leakage Distance	8.7" (220mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A
Reference Voltage Limit - Minimum	Thru 14.4kV
Temperature Rise - Max. at 300A	38° C
Voltage - Maximum	15 kV
Voltage - Radio Interference	Ambient @ 9.41kV
Voltage Rating	15 kV

Logistics

Pallet Quantity	72
Standard Package	1

Product Assets

Catalogs - Type C-Porcelain Cutouts (10A)
Installation Manuals - Standard Cutout Installation Instructions
Literature - SF11036E_HPS CHANCE RUS Cutout Listing
Literature - Switching Line Card_FAQ_2019
Sales Drawings - 110 KV BIL Cutout (SA710-1)
Technical Solutions - CH-C710112PZM-SPEC-EN

Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience (VI10004E)

Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality (VI10005E)

©2024 Hubbell Incorporated. All rights reserved.