



## 15 kV, 110 kV BIL, Type C Standard Porcelain Cutout w/300A Solid Blade

By Chance

Catalog # [C710133LXM](#)

15 kV, 110 kV BIL, Standard Type C Porcelain Cutout with a 300A solid blade, large eyebolt connector and an extended NEMA "B" crossarm bracket.



### Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material

### General

Bracket Type	Extended NEMA "B" for crossarm
Catalog Number	C710133LXM
Description - Replacement	T710-133TM
Fuse Holder Type	Cutout

### Dimensions

Weight	21.76 lb
--------	----------

### Electrical Ratings

BIL	110 kV
Creep and Leakage Distance	8.7" (220mm)
Current Rating	300 A
Reference Voltage Limit - Minimum	Thru 14.4kV
Temperature Rise - Max. at 300A	38° C
Voltage - Maximum	15 kV
Voltage - Radio Interference	Ambient @ 9.41kV
Voltage Rating	15 kV
Withstand Current - Short Time (10 cycles)	12,000 Amps Asym.

### Logistics

Pallet Quantity	72 EA
Standard Package	1

### Product Assets

[Catalogs - Type C-Porcelain Cutouts](#)  
[Installation Manuals - Standard Cutout Installation Instructions](#)  
[Literature - Switching Line Card\\_FAQ\\_2019](#)  
[Literature - HUBBELL® | CHANCE® RUS CUTOUT LISTING](#)  
[Sales Drawings - 110 KV BIL Cutout](#)  
[Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality Experience](#)  
[Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
CH-C710133LXM-SPEC-EN | REV 6/2024