



15 kV, 110 kV BIL, Type C Standard Porcelain Cutout w/200A 12kAIC fuseholder

By Chance

Catalog # [C710143PBM](#)

15 kV, 110 kV BIL, Standard Type C Porcelain Cutout with a 200A, 12kAIC fuseholder, parallel-groove connector and a NEMA "B" crossarm bracket.



Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material

General

Bracket Type	NEMA "B" Heavy Duty for crossarm
Catalog Number	C710143PBM
Description - Replacement	T710-143TM
Fuse Holder Type	Cutout

Dimensions

Weight	21.37 lb
--------	----------

Electrical Ratings

BIL	110 kV
Creep and Leakage Distance	8.7" (220mm)
Current Rating	200 A
Fuselink Current Range	140A to 200A - removable buttonhead fuse link only
Reference Voltage Limit - Minimum	Thru 14.4kV
Temperature Rise - Max. at 300A	38° C
Voltage - Maximum	15 kV
Voltage - Radio Interference	Ambient @ 9.41kV
Voltage Rating	15 kV

Logistics

Pallet Quantity	72 EA
Standard Package	1

Product Assets

[Catalogs - Type C-Porcelain Cutouts](#)
[Installation Manuals - Standard Cutout Installation Instructions](#)
[Literature - Switching Line Card_FAQ_2019](#)
[Literature - HUBBELL® | CHANCE® RUS CUTOUT LISTING](#)
[Sales Drawings - 110 KV BIL Cutout](#)
[Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality Experience](#)
[Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CH-C710143PBM-SPEC-EN | REV 6/2024