



27 kV, 125 kV BIL, Type C Standard Porcelain Cutout w/200A 10kAIC fuseholder

By Chance

Catalog # [C710242PB](#)

27 kV, 125 kV BIL, Standard Type C Porcelain Cutout with a 200A, 10kAIC fuseholder, parallel-groove connector and a NEMA "B" crossarm bracket.



Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material

General

| | |
|---------------------------|----------------------------------|
| Bracket Type | NEMA "B" Heavy Duty for crossarm |
| Catalog Number | C710242PB |
| Description - Replacement | T710-242T |
| Fuse Holder Type | Cutout |
| UPC | 096359239796 |

Dimensions

| | |
|------------|----------------------------------|
| Dimensions | 19.750 in x 13.250 in x 4.120 in |
| Height | 4.12 in |
| Length | 19.75 in |
| Weight | 21.374 lb |
| Width | 13.25 in |

Electrical Ratings

| | |
|-----------------------------------|------------------|
| BIL | 125 kV |
| Creep and Leakage Distance | 12.6" (319mm) |
| Current Rating | 200 A |
| Fuselink Current Range | 140A to 200A |
| Reference Voltage Limit - Minimum | Thru 24.9kV |
| Temperature Rise - Max. at 300A | 33° C |
| Voltage - Maximum | 27 kV |
| Voltage - Radio Interference | Ambient @15.66kV |
| Voltage Rating | 27 kV |

Logistics

| | |
|------------------|----|
| Pallet Quantity | 48 |
| Standard Package | 1 |

Product Assets

[Catalogs - Type C-Porcelain Cutouts](#)
[Installation Manuals - Standard Cutout Installation Instructions](#)
[Literature - Switching Line Card_FAQ_2019](#)
[Literature - HUBBELL® | CHANCE® RUS CUTOUT LISTING](#)
[Sales Drawings - 125KV BIL Cutout](#)
[Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality Experience](#)
[Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CH-C710242PB-SPEC-EN | REV 6/2024