



## 27 kV, 150 kV BIL, Type C Standard Porcelain Cutout w/100A 8kAIC fuseholder

By Chance

Catalog # [C710311EXMS](#)

27 kV, 150 kV BIL, Standard Type C Porcelain Cutout with a 100A, 8kAIC fuseholder, small eyebolt connector and an extended NEMA "B" crossarm bracket.



### Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material

### General

Bracket Type	Extended NEMA "B" for crossarm
Catalog Number	C710311EXMS
Corrosion Resistant?	Yes
Description - Replacement	T710-311TM
Fuse Holder Type	Cutout

### Dimensions

Weight	29.71 lb
--------	----------

### Electrical Ratings

BIL	150 kV
Creep and Leakage Distance	17.3" (440mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A
Reference Voltage Limit - Minimum	No Restrictions thru 24.9kV; *26.4 thru 34.5kV
Temperature Rise - Max. at 300A	35° C
Voltage - Maximum	27 kV
Voltage - Radio Interference	Ambient @22kV
Voltage Rating	27 kV

### Logistics

Pallet Quantity	42 EA
Standard Package	1

### Product Assets

[Catalogs - Type C-Porcelain Cutouts](#)  
[Installation Manuals - Standard Cutout Installation Instructions](#)  
[Literature - Switching Line Card\\_FAQ\\_2019](#)  
[Literature - HUBBELL® | CHANCE® RUS CUTOUT LISTING](#)  
[Sales Drawings - 150KV BIL Cutout](#)  
[Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality Experience](#)  
[Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
CH-C710311EXMS-SPEC-EN | REV 6/2024