



27 kV, 150 kV BIL, Type C Standard Porcelain Cutout w/100A 8kAIC fuseholder

By CHANCE Utility
Catalog # C710311PBM

27 kV, 150 kV BIL, Standard Type C Porcelain Cutout with a 100A, 8kAIC fuseholder, parallel-groove connector and a NEMA "B" crossarm bracket.



*Representative Image

Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material

General

| | |
|---------------------------------------|----------------------------------|
| Bracket Type | NEMA "B" Heavy Duty for crossarm |
| Corrosion Resistant? | No |
| Description - Replacement Fuse Holder | T710-311TM |
| Type | Cutout |

Dimensions

| | |
|--------|----------|
| Weight | 28.97 lb |
|--------|----------|

Electrical Ratings

| | |
|-----------------------------------|--|
| BIL | 150 kV |
| Creep and Leakage Distance | 17.3" (440mm) |
| Current Rating | 100 A |
| Fuselink Current Range | 1A to 100A |
| Reference Voltage Limit - Minimum | No Restrictions thru 24.9kV; *26.4 thru 34.5kV |
| Temperature Rise - Max. at 300A | 35° C |
| Voltage - Maximum | 27 kV |
| Voltage - Radio Interference | Ambient @22kV |
| Voltage Rating | 27 kV |

Logistics

| | |
|------------------|-------|
| Pallet Quantity | 42 EA |
| Standard Package | 1 |

Product Assets

- [Catalogs - Type C-Porcelain Cutouts \(10A\)](#)
- [Installation Manuals - Standard Cutout Installation Instructions](#)
- [Literature - SF11036E_HPS CHANCE RUS Cutout Listing](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Sales Drawings - 150KV BIL Cutout \(SA710-3\)](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience \(VI10004E\)](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality \(VI10005E\)](#)



A proud member of the Hubbell Family.