



## 27 kV, 150 kV BIL, Type C Standard Porcelain Cutout w/100A 8kAIC fuseholder

By CHANCE Utility  
Catalog # [C710311PDMS](#)

27 kV, 150 kV BIL, Standard Type C Porcelain Cutout with a 100A, 8kAIC fuseholder, parallel-groove connector and a D-shape pole mounting bracket.



\*Representative Image

### Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material

### General

Bracket Type	D-shape for pole mounting
Corrosion Resistant?	Yes
Description - Replacement Fuse Holder	T710-311TM
Type	Cutout

### Dimensions

Weight	33.8 lb
--------	---------

### Electrical Ratings

BIL	150 kV
Creep and Leakage Distance	17.3" (440mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A
Reference Voltage Limit - Minimum	No Restrictions thru 24.9kV; *26.4 thru 34.5kV
Temperature Rise - Max. at 300A	35° C
Voltage - Maximum	27 kV
Voltage - Radio Interference	Ambient @22kV
Voltage Rating	27 kV

### Logistics

Pallet Quantity	42 EA
Standard Package	1

### Product Assets

[Catalogs - Type C-Porcelain Cutouts \(10A\)](#)  
[Installation Manuals - Standard Cutout Installation Instructions](#)  
[Literature - SF11036E\\_HPS CHANCE RUS Cutout Listing](#)  
[Literature - Switching Line Card\\_FAQ\\_2019](#)  
[Sales Drawings - 150KV BIL Cutout \(SA710-3\)](#)  
[Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience \(VI10004E\)](#)  
[Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality \(VI10005E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CH-C710311PDMS-SPEC-EN | REV 1/2024