



27 kV, 150 kV BIL, Type C Standard Porcelain Cutout w/300A Solid Blade

By CHANCE Utility
Catalog # C710333EXMS

27 kV, 150 kV BIL, Standard Type C Porcelain Cutout with a 300A solid blade, small eyebolt connector and an extended NEMA "B" crossarm bracket.



*Representative Image

Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material

General

Bracket Type	Extended NEMA "B" for crossarm
Corrosion Resistant?	Yes
Description - Replacement Fuse Holder	T710-333TM
Type	Cutout

Dimensions

Weight	30.11 lb
--------	----------

Electrical Ratings

BIL	150 kV
Creep and Leakage Distance	17.3" (440mm)
Current Rating	300 A
Reference Voltage Limit - Minimum	No Restrictions thru 24.9kV; *26.4 thru 34.5kV
Temperature Rise - Max. at 300A	35° C
Voltage - Maximum	27 kV
Voltage - Radio Interference	Ambient @22kV
Voltage Rating	27 kV
Withstand Current - Short Time (10 cycles)	12,000 Amps Asym.

Logistics

Pallet Quantity	42 EA
Standard Package	1

Product Assets

- [Catalogs - Type C-Porcelain Cutouts \(10A\)](#)
- [Installation Manuals - Standard Cutout Installation Instructions](#)
- [Literature - SF11036E_HPS CHANCE RUS Cutout Listing](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Sales Drawings - 150KV BIL Cutout \(SA710-3\)](#)
- [Technical Solutions - CH-C710333EXMS-SPEC-EN](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience \(VI10004E\)](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality \(VI10005E\)](#)



A proud member of the Hubbell Family.