



## 27 kV, 150 kV BIL, Type C Standard Porcelain Cutout w/300A Solid Blade

By Chance

Catalog # [C710333EZMS](#)

27 kV, 150 kV BIL, Standard Type C Porcelain Cutout with a 300A solid blade, small eyebolt connector and no bracket.



### Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material

### General

Bracket Type	No Bracket
Catalog Number	C710333EZMS
Corrosion Resistant?	Yes
Description - Replacement	T710-333TM
Fuse Holder Type	Cutout

### Dimensions

Weight	26.36 lb
--------	----------

### Electrical Ratings

BIL	150 kV
Creep and Leakage Distance	17.3" (440mm)
Current Rating	300 A
Reference Voltage Limit - Minimum	No Restrictions thru 24.9kV; *26.4 thru 34.5kV
Temperature Rise - Max. at 300A	35° C
Voltage - Maximum	27 kV
Voltage - Radio Interference	Ambient @22kV
Voltage Rating	27 kV
Withstand Current - Short Time (10 cycles)	12,000 Amps Asym.

### Logistics

Pallet Quantity	42 EA
Standard Package	1

### Product Assets

- [Catalogs - Type C-Porcelain Cutouts](#)
- [Installation Manuals - Standard Cutout Installation Instructions](#)
- [Literature - Switching Line Card\\_FAQ\\_2019](#)
- [Literature - HUBBELL® | CHANCE® RUS CUTOUT LISTING](#)
- [Sales Drawings - 150KV BIL Cutout](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality Experience](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
CH-C710333EZMS-SPEC-EN | REV 6/2024