



27 kV, 150 kV BIL, Type C Standard Porcelain Cutout w/300A Solid Blade

By Chance

Catalog # [C710333PBM](#)

27 kV, 150 kV BIL, Standard Type C Porcelain Cutout with a 300A solid blade, parallel-groove connector and a NEMA "B" crossarm bracket.



Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material

General

Bracket Type	NEMA "B" Heavy Duty for crossarm
Catalog Number	C710333PBM
Corrosion Resistant?	No
Description - Replacement	T710-333TM
Fuse Holder Type	Cutout

Dimensions

Weight	29.37 lb
--------	----------

Electrical Ratings

BIL	150 kV
Creep and Leakage Distance	17.3" (440mm)
Current Rating	300 A
Reference Voltage Limit - Minimum	No Restrictions thru 24.9kV; *26.4 thru 34.5kV
Temperature Rise - Max. at 300A	35° C
Voltage - Maximum	27 kV
Voltage - Radio Interference	Ambient @22kV
Voltage Rating	27 kV
Withstand Current - Short Time (10 cycles)	12,000 Amps Asym.

Logistics

Pallet Quantity	42 EA
Standard Package	1

Product Assets

[Catalogs - Type C-Porcelain Cutouts](#)
[Installation Manuals - Standard Cutout Installation Instructions](#)
[Literature - Switching Line Card_FAQ_2019](#)
[Literature - HUBBELL® | CHANCE® RUS CUTOUT LISTING](#)
[Sales Drawings - 150KV BIL Cutout](#)
[Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality Experience](#)
[Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CH-C710333PBM-SPEC-EN | REV 6/2024