



27 kV, 125 kV BIL, Type C Standard Porcelain Cutout w/300A Solid Blade

By CHANCE Utility
Catalog # C710233LD

27 kV, 125 kV BIL, Standard Type C Porcelain Cutout with a 300A solid blade, large eyebolt connector and a D-shape pole mounting bracket.



*Representative Image

Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material

General

Bracket Type	D-shape for pole mounting
Description - Replacement Fuse Holder Type	T710-233T Cutout

Dimensions

Weight	28.38 lb
--------	----------

Electrical Ratings

BIL	125 kV
Creep and Leakage Distance	12.6" (319mm)
Current Rating	300 A
Reference Voltage Limit - Minimum	Thru 24.9kV
Temperature Rise - Max. at 300A	33° C
Voltage - Maximum	27 kV
Voltage - Radio Interference	Ambient @15.66kV
Voltage Rating	27 kV
Withstand Current - Short Time (10 cycles)	12,000 Amps Asym.

Logistics

Pallet Quantity	48 EA
Standard Package	1

Product Assets

- [Catalogs - Type C-Porcelain Cutouts \(10A\)](#)
- [Installation Manuals - Standard Cutout Installation Instructions](#)
- [Literature - SF11036E_HPS CHANCE RUS Cutout Listing](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Sales Drawings - 125KV BIL Cutout \(SA710-2\)](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience \(VI10004E\)](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality \(VI10005E\)](#)



A proud member of the Hubbell Family.