



## 36 kV, 170 kV BIL, Type C Standard Porcelain Cutout w/300A Solid Blade

By CHANCE Utility  
Catalog # [C710733LBM](#)

36 kV, 170 kV BIL, Standard Type C Porcelain Cutout with a 300A, 12kAIC solid blade, large eyebolt connector and a NEMA "B" crossarm bracket.



\*Representative Image

### Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material

### General

Bracket Type	NEMA "B" Heavy Duty for crossarm
Corrosion Resistant?	No
Description - Replacement Fuse Holder	T710-733TM
Type	Cutout

### Dimensions

Weight	37.05 lb
--------	----------

### Electrical Ratings

BIL	170 kV
Creep and Leakage Distance	28.4" (720mm)
Current Rating	300 A
Reference Voltage Limit - Minimum	Thru 34.5kV
Voltage - Maximum	36 kV
Voltage Rating	36 kV
Withstand Current - Short Time (10 cycles)	12,000 Amps Asym.

### Logistics

Pallet Quantity	24 EA
Standard Package	1

### Product Assets

[Catalogs - Type C-Porcelain Cutouts \(10A\)](#)  
[Installation Manuals - Standard Cutout Installation Instructions](#)  
[Literature - SF11036E\\_HPS CHANCE RUS Cutout Listing](#)  
[Literature - Switching Line Card\\_FAQ\\_2019](#)  
[Sales Drawings - 170KV BIL Cutout \(730MM\) \(SA710-7\)](#)  
[Technical Solutions - CH-C710733LBM-SPEC-EN](#)  
[Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience \(VI10004E\)](#)  
[Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality \(VI10005E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CH-C710733LBM-SPEC-EN | REV 1/2024