



27 kV, 150 kV BIL, Type C Standard Porcelain Cutout w/100A 8kAIC fuseholder

By Chance
Catalog # [C710311LB](#)

27 kV, 150 kV BIL, Standard Type C Porcelain Cutout with a 100A, 8kAIC fuseholder, large eyebolt connector and a NEMA "B" crossarm bracket.

Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 – 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material

General

Bracket Type	NEMA "B" Heavy Duty for crossarm
Catalog Number	C710311LB
Corrosion Resistant?	No
Description - Replacement	T710-311T
Fuse Holder	
Type	Cutout
UPC	096359029854

Dimensions

Weight	26.323 lb
--------	-----------

Electrical Ratings

BIL	150 kV
Creep and Leakage Distance	17.3" (440mm)



Current Rating	100 A
Fuselink Current Range	1A to 100A
Reference Voltage Limit - Minimum	No Restrictions thru 24.9kV; *26.4 thru 34.5kV
Temperature Rise - Max. at 300A	35° C
Voltage - Maximum	27 kV
Voltage - Radio Interference	Ambient @22kV
Voltage Rating	27 kV

Logistics

Pallet Quantity	42
Standard Package	1

Product Assets

- [Catalogs - Type C-Porcelain Cutouts](#)
- [Installation Manuals - Standard Cutout Installation Instructions](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Literature - HUBBELL® | CHANCE® RUS CUTOUT LISTING](#)
- [Sales Drawings - 150KV BIL Cutout](#)
- [Specifications - C710311LB](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)



A Hubbell brand