



15 kV, 110 kV BIL, Type C Standard Porcelain Cutout / Arrester Combination w/300A Solid Blade

By CHANCE Utility
Catalog # C71DM133EXM

15 kV, 110 kV BIL, Standard Type C Porcelain Cutout / Arrester Combination with a 300A solid blade, small eyebolt connector and an extended NEMA "B" crossarm bracket.



*Representative Image

Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- Ohio Brass Distribution Class Arresters in Standard, Heavy and Riser Pole Duty Ratings

General

Bracket Type	Extended NEMA "B" for crossarm
Description - Replacement Fuse Holder	T710-133TM
Type	Cutout

Electrical Ratings

BIL	110 kV
Creep and Leakage Distance	8.7" (220mm)
Current Rating	300 A
Reference Voltage Limit - Minimum	Thru 14.4kV
Temperature Rise - Max. at 300A	38° C
Voltage - Maximum	15 kV
Voltage - Radio Interference	Ambient @ 9.41kV
Voltage Rating	15 kV
Withstand Current - Short Time (10 cycles)	12,000 Amps Asym.

Logistics

Pallet Quantity	18 EA
Standard Package	1

Product Assets

- [Catalogs - Type C-Porcelain Cutouts \(10A\)](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Sales Drawings - 110 KV BIL Cutout/ Arrester \(SA71DL1_B\)](#)
- [Technical Solutions - CH-C71DM133EXM-SPEC-EN](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience \(VI10004E\)](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality \(VI10005E\)](#)



A proud member of the Hubbell Family.