



27 kV, 150 kV BIL, Type C Standard Porcelain Cutout w/200A 10kAIC fuseholder

By CHANCE Utility
Catalog # C710342PX

27 kV, 150 kV BIL, Standard Type C Porcelain Cutout with a 200A, 10kAIC fuseholder, parallel-groove connector and an extended NEMA "B" crossarm bracket.



*Representative Image

Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material

General

Bracket Type	Extended NEMA "B" for crossarm
Corrosion Resistant?	No
Description - Replacement Fuse Holder	T710-342T
Type	Cutout
UPC	096359491552

Dimensions

Weight	30.68 lb
--------	----------

Electrical Ratings

BIL	150 kV
Creep and Leakage Distance	17.3" (440mm)
Current Rating	200 A
Fuselink Current Range	140A to 200A
Reference Voltage Limit - Minimum	No Restrictions thru 24.9kV; *26.4 thru 34.5kV
Temperature Rise - Max. at 300A	35° C
Voltage - Maximum	27 kV
Voltage - Radio Interference	Ambient @22kV
Voltage Rating	27 kV

Logistics

Pallet Quantity	42 EA
Standard Package	1

Product Assets

[Catalogs - Type C-Porcelain Cutouts \(10A\)](#)
[Installation Manuals - Standard Cutout Installation Instructions](#)
[Literature - SF11036E_HPS CHANCE RUS Cutout Listing](#)
[Literature - Switching Line Card_FAQ_2019](#)
[Sales Drawings - 150KV BIL Cutout \(SA710-3\)](#)
[Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience \(VI10004E\)](#)
[Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality \(VI10005E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CH-C710342PX-SPEC-EN | REV 1/2024