



36 kV, 170 kV BIL, Type C Standard Porcelain Cutout w/100A 12kAIC fuseholder

By CHANCE Utility
Catalog # C710613PDMS



*Representative Image

Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material

General

Bracket Type	D-shape for pole mounting
Corrosion Resistant?	Yes
Description - Replacement Fuse Holder	T710-613TM
Type	Cutout

Dimensions

Weight	36.6 lb
--------	---------

Electrical Ratings

BIL	170 kV
Creep and Leakage Distance	26" (660mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A - removable buttonhead fuse link only
Reference Voltage Limit - Minimum	Thru 34.5kV
Voltage - Maximum	36 kV
Voltage Rating	36 kV

Logistics

Pallet Quantity	24 EA
Standard Package	1

Product Assets

- [Catalogs - Type C-Porcelain Cutouts \(10A\)](#)
- [Installation Manuals - Standard Cutout Installation Instructions](#)
- [Literature - SF11036E_HPS CHANCE RUS Cutout Listing](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Sales Drawings - 170KV BIL Cutout \(660MM\) \(SA710-6\)](#)
- [Technical Solutions - CH-C710613PDMS-SPEC-EN](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience \(VI10004E\)](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality \(VI10005E\)](#)



A proud member of the Hubbell Family.