



27 kV, 150 kV BIL, Type C Standard Porcelain Cutout / Arrester Combination w/100A 8kAIC fuseholder

By CHANCE Utility
Catalog # [C71DN311LDMS](#)

27 kV, 150 kV BIL, Standard Type C Porcelain Cutout / Arrester Combination with a 100A, 8kAIC fuseholder, large eyebolt connector and a D-shape pole mounting bracket.



*Representative Image

Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- Ohio Brass Distribution Class Arresters in Standard, Heavy and Riser Pole Duty Ratings

General

Bracket Type	D-shape for pole mounting
Corrosion Resistant?	Yes
Description - Replacement Fuse Holder	T710-311TM
Type	Cutout

Electrical Ratings

BIL	150 kV
Creep and Leakage Distance	17.3" (440mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A
Reference Voltage Limit - Minimum	No Restrictions thru 24.9kV; *26.4 thru 34.5kV
Temperature Rise - Max. at 300A	35° C
Voltage - Maximum	27 kV
Voltage - Radio Interference	Ambient @22kV
Voltage Rating	27 kV

Logistics

Pallet Quantity	18 EA
Standard Package	1

Product Assets

- [Catalogs - Type C-Porcelain Cutouts \(10A\)](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Sales Drawings - Cutout, Arrester 27 KV, 150 KV BIL \(PSSA71DN3\)](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience \(VI10004E\)](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality \(VI10005E\)](#)



A proud member of the Hubbell Family.