



## 27 kV, 170 kV BIL, Type C Standard Porcelain Cutout / Arrester Combination

By Chance

Catalog # [C71EP743EXM](#)

27 kV, 170 kV BIL, Standard Type C Porcelain Cutout / Arrester Combination with a 200A, 12kAIC fuseholder, small eyebolt connector and an extended NEMA "B" crossarm bracket.



### Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- Ohio Brass Distribution Class Arresters in Standard, Heavy and Riser Pole Duty Ratings

### General

Bracket Type	Extended NEMA "B" for crossarm
Catalog Number	C71EP743EXM
Corrosion Resistant?	No
Description - Replacement	T710-743TM
Fuse Holder Type	Cutout

### Electrical Ratings

BIL	170 kV
Creep and Leakage Distance	28.4" (720mm)
Current Rating	200 A
Fuselink Current Range	140A to 200A - removable buttonhead fuse link only
Reference Voltage Limit - Minimum	No Restrictions thru 24.9kV; *26.4 thru 34.5kV
Voltage - Maximum	27 kV
Voltage Rating	27 kV

### Logistics

Standard Package	1
------------------	---

### Product Assets

[Catalogs - Type C-Porcelain Cutouts](#)

[Literature - Switching Line Card\\_FAQ\\_2019](#)

[Sales Drawings - 170 KV BIL \(720MM\) Cutout/ Arrester](#)

[Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality](#)

[Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)



A Hubbell brand