



15 kV, 110 kV BIL, Type C Standard Porcelain Cutout / Arrester Combination w/300A Solid Blade

By CHANCE Utility
Catalog # [C71DL133EBM](#)

15 kV, 110 kV BIL, Standard Type C Porcelain Cutout / Arrester Combination with a 300A solid blade, small eyebolt connector and a NEMA "B" crossarm bracket.



*Representative Image

Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- Ohio Brass Distribution Class Arresters in Standard, Heavy and Riser Pole Duty Ratings

General

| | |
|---------------------------------------|----------------------------------|
| Bracket Type | NEMA "B" Heavy Duty for crossarm |
| Description - Replacement Fuse Holder | T710-133TM |
| Type | Cutout |

Electrical Ratings

| | |
|--|-------------------|
| BIL | 110 kV |
| Creep and Leakage Distance | 8.7" (220mm) |
| Current Rating | 300 A |
| Reference Voltage Limit - Minimum | Thru 14.4kV |
| Temperature Rise - Max. at 300A | 38° C |
| Voltage - Maximum | 15 kV |
| Voltage - Radio Interference | Ambient @ 9.41kV |
| Voltage Rating | 15 kV |
| Withstand Current - Short Time (10 cycles) | 12,000 Amps Asym. |

Logistics

| | |
|------------------|-------|
| Pallet Quantity | 18 EA |
| Standard Package | 1 |

Product Assets

- [Catalogs - Type C-Porcelain Cutouts \(10A\)](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Sales Drawings - 110 KV BIL Cutout/ Arrester \(SA71DL1_B\)](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience \(VI10004E\)](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality \(VI10005E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CH-C71DL133EBM-SPEC-EN | REV 1/2024