



# 36 kV, 170 kV BIL, Type C Standard Porcelain Cutout / Arrester Combination

By CHANCE Utility  
Catalog # [C71FP613PXMS](#)

36 kV, 170 kV BIL, Standard Type C Porcelain Cutout / Arrester Combination with a 100A, 11.2kAIC fuseholder, parallel-groove connector and an extended NEMA "B" crossarm bracket.



\*Representative Image

## Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- Ohio Brass Distribution Class Arresters in Standard, Heavy and Riser Pole Duty Ratings

## General

Bracket Type	Extended NEMA "B" for crossarm
Corrosion Resistant?	Yes
Description - Replacement Fuse Holder	T710-613TM
Type	Cutout

## Electrical Ratings

BIL	170 kV
Creep and Leakage Distance	26" (660mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A - removable buttonhead fuse link only
Reference Voltage Limit - Minimum	Thru 34.5kV
Voltage - Maximum	36 kV
Voltage Rating	36 kV

## Logistics

Standard Package	1
------------------	---

## Product Assets

- [Catalogs - Type C-Porcelain Cutouts \(10A\)](#)
- [Literature - Switching Line Card\\_FAQ\\_2019](#)
- [Sales Drawings - 170 KV BIL \(660 MM\) Cutout/ Arrester Combo \(PSSA71DN6\\_B\)](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience \(VI10004E\)](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality \(VI10005E\)](#)



A proud member of the Hubbell Family.