



36 kV, 170 kV BIL, Type C Standard Porcelain Cutout / Arrester Combination w/300A Solid Blade

By CHANCE Utility
Catalog # C71FP733PDM

36 kV, 170 kV BIL, Standard Type C Porcelain Cutout / Arrester Combination with a 300A, 12kAIC solid blade, parallel-groove connector and a D-shape pole mounting bracket.



*Representative Image

Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- Ohio Brass Distribution Class Arresters in Standard, Heavy and Riser Pole Duty Ratings

General

| | |
|---------------------------------------|---------------------------|
| Bracket Type | D-shape for pole mounting |
| Corrosion Resistant? | No |
| Description - Replacement Fuse Holder | T710-733TM |
| Type | Cutout |

Electrical Ratings

| | |
|--|-------------------|
| BIL | 170 kV |
| Creep and Leakage Distance | 28.4" (720mm) |
| Current Rating | 300 A |
| Reference Voltage Limit - Minimum | Thru 34.5kV |
| Voltage - Maximum | 36 kV |
| Voltage Rating | 36 kV |
| Withstand Current - Short Time (10 cycles) | 12,000 Amps Asym. |

Logistics

| | |
|------------------|---|
| Standard Package | 1 |
|------------------|---|

Product Assets

[Catalogs - Type C-Porcelain Cutouts \(10A\)](#)
[Literature - Switching Line Card_FAQ_2019](#)
[Sales Drawings - 170 KV BIL \(720MM\) Cutout/ Arrester \(SA71DN7_B\)](#)

[Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience \(VI10004E\)](#)

[Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality \(VI10005E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CH-C71FP733PDM-SPEC-EN | REV 1/2024