



# 27 kV, 170 kV BIL, Type C Standard Porcelain Cutout / Arrester Combination

By CHANCE Utility  
Catalog # [C71FP743EXMS](#)

27 kV, 170 kV BIL, Standard Type C Porcelain Cutout / Arrester Combination with a 200A, 12kAIC fuseholder, small eyebolt connector and an extended NEMA "B" crossarm bracket.



\*Representative Image

### Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- Ohio Brass Distribution Class Arresters in Standard, Heavy and Riser Pole Duty Ratings

### General

Bracket Type	Extended NEMA "B" for crossarm
Corrosion Resistant?	Yes
Description - Replacement Fuse Holder	T710-743TM
Type	Cutout

### Electrical Ratings

BIL	170 kV
Creep and Leakage Distance	28.4" (720mm)
Current Rating	200 A
Fuselink Current Range	140A to 200A - removable buttonhead fuse link only
Reference Voltage Limit - Minimum	No Restrictions thru 24.9kV; *26.4 thru 34.5kV
Voltage - Maximum	27 kV
Voltage Rating	27 kV

### Logistics

Standard Package	1
------------------	---

### Product Assets

- [Catalogs - Type C-Porcelain Cutouts \(10A\)](#)
- [Literature - Switching Line Card\\_FAQ\\_2019](#)
- [Sales Drawings - 170 KV BIL \(720MM\) Cutout/ Arrester \(SA71DN7\\_B\)](#)
- [Technical Solutions - CH-C71FP743EXMS-SPEC-EN](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience \(VI10004E\)](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality \(VI10005E\)](#)



A proud member of the Hubbell Family.