



15 kV, 110 kV BIL, Type C Linkbreak Porcelain Cutout w/100A 10kAIC fuseholder

By Chance
Catalog # [C720112ED](#)

15 kV, 110 kV BIL, Linkbreak Type C Porcelain Cutout with a 100A, 10kAIC fuseholder, small eyebolt connector and a D-shape pole mounting bracket.



Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material

General

| | |
|---------------------------|---------------------------|
| Bracket Type | D-shape for pole mounting |
| Catalog Number | C720112ED |
| Description - Replacement | T720-112T |
| Fuse Holder Type | Cutout |

Dimensions

| | |
|--------|----------|
| Weight | 25.53 lb |
|--------|----------|

Electrical Ratings

| | |
|-----------------------------------|------------------|
| BIL | 110 kV |
| Creep and Leakage Distance | 8.7" (220mm) |
| Current Rating | 100 A |
| Fuselink Current Range | 1A to 100A |
| Reference Voltage Limit - Minimum | Thru 14.4kV |
| Temperature Rise - Max. at 300A | 38° C |
| Voltage - Maximum | 15 kV |
| Voltage - Radio Interference | Ambient @ 9.41kV |
| Voltage Rating | 15 kV |

Logistics

| | |
|------------------|-------|
| Pallet Quantity | 72 EA |
| Standard Package | 1 |

Product Assets

- [Catalogs - Type C-Porcelain Cutouts](#)
- [Installation Manuals - Link Break Cutout Installation Instructions](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Literature - HUBBELL® | CHANCE® RUS CUTOUT LISTING](#)
- [Sales Drawings - Cutout, Linkbreak 110 KV BIL](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality Experience](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CH-C720112ED-SPEC-EN | REV 6/2024