



## 27 kV, 125 kV BIL, Type C Standard Porcelain Cutout / Arrester Combination

By CHANCE Utility  
Catalog # [C71DN211LX](#)

27 kV, 125 kV BIL, Standard Type C Porcelain Cutout / Arrester Combination with a 100A, 8kAIC fuseholder, large eyebolt connector and an extended NEMA "B" crossarm bracket.



\*Representative Image

### Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- Ohio Brass Distribution Class Arresters in Standard, Heavy and Riser Pole Duty Ratings

### General

Bracket Type	Extended NEMA "B" for crossarm
Description - Replacement Fuse Holder	T710-211T
Type	Cutout

### Electrical Ratings

BIL	125 kV
Creep and Leakage Distance	12.6" (319mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A
Reference Voltage Limit - Minimum	Thru 24.9kV
Temperature Rise - Max. at 300A	33° C
Voltage - Maximum	27 kV
Voltage - Radio Interference	Ambient @15.66kV
Voltage Rating	27 kV

### Logistics

Pallet Quantity	18 EA
Standard Package	1

### Product Assets

[Catalogs - Type C-Porcelain Cutouts \(10A\)](#)  
[Literature - Switching Line Card\\_FAQ\\_2019](#)  
[Sales Drawings - 125 KV BIL Cutout / Arrester \(SA71DN2\\_A\)](#)  
[Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience \(VI10004E\)](#)  
[Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality \(VI10005E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CH-C71DN211LX-SPEC-EN | REV 1/2024