



# 22/36.4 kV, 150 kV BIL, Type C Linkbreak Porcelain Cutout w/100A 8kAIC fuseholder

By Chance  
Catalog # [C720311EB](#)

22/36.4 kV, 150 kV BIL, Linkbreak Type C Porcelain Cutout with a 100A, 8kAIC fuseholder, small eyebolt connector and a NEMA "B" crossarm bracket.



## Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material

## General

Bracket Type	NEMA "B" Heavy Duty for crossarm
Catalog Number	C720311EB
Corrosion Resistant?	No
Description - Replacement	T720-311T
Fuse Holder Type	Cutout

## Dimensions

Weight	29.2 lb
--------	---------

## Electrical Ratings

BIL	150 kV
Creep and Leakage Distance	17.3" (440mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A
Reference Voltage Limit - Minimum	No Restrictions thru 20.8kV; *22.8 thru 34.5kV
Temperature Rise - Max. at 300A	35° C
Voltage - Radio Interference	Ambient @22kV
Voltage Rating	22/36.4 kV

## Logistics

Pallet Quantity	42 EA
Standard Package	1

## Product Assets

- [Catalogs - Type C-Porcelain Cutouts](#)
- [Installation Manuals - Link Break Cutout Installation Instructions](#)
- [Literature - Switching Line Card\\_FAQ\\_2019](#)
- [Literature - HUBBELL® | CHANCE® RUS CUTOUT LISTING](#)
- [Sales Drawings - Cutout, Linkbreak 125 KV BIL](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality Experience](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
CH-C720311EB-SPEC-EN | REV 6/2024