



## 22/36.4 kV, 170 kV BIL, Type C Linkbreak Porcelain Cutout w/100A 12kAIC fuseholder

By CHANCE Utility  
Catalog # C720613LD

22/36.4 kV, 170 kV BIL, Linkbreak Type C Porcelain Cutout with a 100A, 11.2kAIC fuseholder, large eyebolt connector and a D-shape pole mounting bracket.



\*Representative Image

### Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material

### General

Bracket Type	D-shape for pole mounting
Corrosion Resistant?	No
Description - Replacement Fuse Holder	T720-613T
Type	Cutout

### Dimensions

Weight	37.28 lb
--------	----------

### Electrical Ratings

BIL	170 kV
Creep and Leakage Distance	26" (660mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A - removable buttonhead fuse link only
Reference Voltage Limit - Minimum	No Restrictions thru 20.8kV; *22.8 thru 34.5kV
Voltage Rating	22/36.4 kV

### Logistics

Standard Package	1
------------------	---

### Product Assets

[Catalogs - Type C-Porcelain Cutouts \(10A\)](#)  
[Installation Manuals - Link Break Cutout Installation Instructions](#)  
[Literature - SF11036E\\_HPS CHANCE RUS Cutout Listing](#)  
[Literature - Switching Line Card\\_FAQ\\_2019](#)  
[Sales Drawings - Cutout, Linkbreak 125 KV BIL \(SA720-6\)](#)  
[Technical Solutions - CH-C720613LD-SPEC-EN](#)  
[Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience \(VI10004E\)](#)  
[Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality \(VI10005E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CH-C720613LD-SPEC-EN | REV 1/2024