



## 36 kV, 170 kV BIL, Type C Standard Porcelain Cutout / Arrester Combination w/300A Solid Blade

By Chance

Catalog # [C71EP633PDMS](#)

36 kV, 170 kV BIL, Standard Type C Porcelain Cutout / Arrester Combination with a 300A solid blade, parallel-groove connector and a D-shape pole mounting bracket.



### Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- Ohio Brass Distribution Class Arresters in Standard, Heavy and Riser Pole Duty Ratings

### General

Bracket Type	D-shape for pole mounting
Catalog Number	C71EP633PDMS
Corrosion Resistant?	Yes
Description - Replacement	T710-633TM
Fuse Holder Type	Cutout

### Electrical Ratings

BIL	170 kV
Creep and Leakage Distance	26" (660mm)
Current Rating	300 A
Reference Voltage Limit - Minimum	Thru 34.5kV
Voltage - Maximum	36 kV
Voltage Rating	36 kV
Withstand Current - Short Time (10 cycles)	12,000 Amps Asym.

### Logistics

Standard Package	1
------------------	---

### Product Assets

[Catalogs - Type C-Porcelain Cutouts](#)

[Literature - Switching Line Card\\_FAQ\\_2019](#)

[Sales Drawings - 170 KV BIL \(660 MM\) Cutout/ Arrester Combo](#)

[Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality](#)

[Video - Hubbell Power Systems Cutout Seminar, Part 2:](#)

[Experience](#)



A Hubbell brand