



27 kV, 150 kV BIL, Type C Standard Porcelain Cutout / Arrester Combination

By Chance

Catalog # [C71FN342LB](#)

27 kV, 150 kV BIL, Standard Type C Porcelain Cutout / Arrester Combination with a 200A, 10kAIC fuseholder, large eyebolt connector and a NEMA "B" crossarm bracket.



Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- Ohio Brass Distribution Class Arresters in Standard, Heavy and Riser Pole Duty Ratings

General

Bracket Type	NEMA "B" Heavy Duty for crossarm
Catalog Number	C71FN342LB
Corrosion Resistant?	No
Description - Replacement	T710-342T
Fuse Holder Type	Cutout

Electrical Ratings

BIL	150 kV
Creep and Leakage Distance	17.3" (440mm)
Current Rating	200 A
Fuselink Current Range	140A to 200A
Reference Voltage Limit - Minimum	No Restrictions thru 24.9kV; *26.4 thru 34.5kV
Temperature Rise - Max. at 300A	35° C
Voltage - Maximum	27 kV
Voltage - Radio Interference	Ambient @22kV
Voltage Rating	27 kV

Logistics

Standard Package 1

Product Assets

[Catalogs - Type C-Porcelain Cutouts](#)

[Literature - Switching Line Card_FAQ_2019](#)

[Sales Drawings - Cutout, Arrester 27 KV, 150 KV BIL](#)

[Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality](#)

[Video - Hubbell Power Systems Cutout Seminar, Part 2:](#)

[Experience](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CH-C71FN342LB-SPEC-EN | REV 6/2024