



## 22/36.4 kV, 150 kV BIL, Type C Linkbreak Porcelain Cutout / Arrester Combination w/100A 8kAIC fuseholder

By Chance

Catalog # [C72EP311PBS](#)

22/36.4 kV, 150 kV BIL, Linkbreak Type C Porcelain Cutout / Arrester Combination with a 100A, 8kAIC fuseholder, parallel-groove connector and a NEMA "B" crossarm bracket.



### Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- Ohio Brass Distribution Class Arresters in Standard, Heavy and Riser Pole Duty Ratings

### General

Bracket Type	NEMA "B" Heavy Duty for crossarm
Catalog Number	C72EP311PBS
Corrosion Resistant?	Yes
Description - Replacement	T720-311T
Fuse Holder Type	Cutout

### Electrical Ratings

BIL	150 kV
Creep and Leakage Distance	17.3" (440mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A
Reference Voltage Limit - Minimum	No Restrictions thru 20.8kV; *22.8 thru 34.5kV
Temperature Rise - Max. at 300A	35° C
Voltage - Radio Interference	Ambient @22kV
Voltage Rating	22/36.4 kV

### Logistics

Standard Package 1

### Product Assets

[Catalogs - Type C-Porcelain Cutouts](#)

[Literature - Switching Line Card\\_FAQ\\_2019](#)

[Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality](#)

[Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)



A Hubbell brand