



# 15 kV, 110 kV BIL, Type C Loadbreak Porcelain Cutout w/300A Solid Blade

By Chance  
Catalog # [C730133E](#)

15 kV, 110 kV BIL, Loadbreak Type C Porcelain Cutout with a 300A solid blade, small eyebolt connector and no bracket.



## Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- Non Interchangeable Mounting Assembly

## General

Bracket Type	No Bracket
Catalog Number	C730133E
Description - Replacement	T730-133T
Fuse Holder Type	Cutout

## Dimensions

Weight	22.96 lb
--------	----------

## Electrical Ratings

BIL	110 kV
Creep and Leakage Distance	8.7" (220mm)
Current Rating	300 A
Reference Voltage Limit - Minimum	Thru 14.4kV
Temperature Rise - Max. at 300A	39° C
Voltage - Maximum	15 kV
Voltage - Radio Interference	Ambient @ 9.41kV
Voltage Rating	15 kV
Withstand Current - Short Time (10 cycles)	12,000 Amps Asym.

## Logistics

Pallet Quantity	24 EA
Standard Package	1

## Product Assets

- [Catalogs - Type C-Porcelain Cutouts](#)
- [Installation Manuals - Load Break Cutout Installation Instructions](#)
- [Literature - Switching Line Card\\_FAQ\\_2019](#)
- [Literature - HUBBELL® | CHANCE® RUS CUTOUT LISTING](#)
- [Sales Drawings - Cutout, LDBK, 15kV, 110 BIL](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality Experience](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
CH-C730133E-SPEC-EN | REV 6/2024