



27 kV, 170 kV BIL, Type C Standard Porcelain Cutout / Arrester Combination

By Chance
Catalog # [C71FP743PDMS](#)

27 kV, 170 kV BIL, Standard Type C Porcelain Cutout / Arrester Combination with a 200A, 12kAIC fuseholder, parallel-groove connector and a D-shape pole mounting bracket.

Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 – 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- Ohio Brass Distribution Class Arresters in Standard, Heavy and Riser Pole Duty Ratings

General

Bracket Type	D-shape for pole mounting
Catalog Number	C71FP743PDMS
Corrosion Resistant?	Yes
Description - Replacement	T710-743TM
Fuse Holder	
Type	Cutout

Electrical Ratings

BIL	170 kV
-----	--------



Creep and Leakage Distance	28.4" (720mm)
Current Rating	200 A
Fuselink Current Range	140A to 200A - removable buttonhead fuse link only
Reference Voltage Limit - Minimum	No Restrictions thru 24.9kV; *26.4 thru 34.5kV
Voltage - Maximum	27 kV
Voltage Rating	27 kV

Logistics

Standard Package	1
------------------	---

Product Assets

- [Catalogs - Type C-Porcelain Cutouts](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Sales Drawings - 170 KV BIL \(720MM\) Cutout/ Arrester](#)
- [Specifications - C71FP743PDMS](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)



A Hubbell brand