



# 15 kV, 110 kV BIL, Type C Loadbreak Porcelain Cutout w/300A Solid Blade

By CHANCE Utility  
Catalog # C730133LD

15 kV, 110 kV BIL, Loadbreak Type C Porcelain Cutout with a 300A solid blade, large eyebolt connector and a D-shape pole mounting bracket.



\*Representative Image

### Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- Non Interchangeable Mounting Assembly

### General

Bracket Type	D-shape for pole mounting
Description - Replacement Fuse Holder	T730-133T
Type	Cutout

### Dimensions

Weight	30.78 lb
--------	----------

### Electrical Ratings

BIL	110 kV
Creep and Leakage Distance	8.7" (220mm)
Current Rating	300 A
Reference Voltage Limit - Minimum	Thru 14.4kV
Temperature Rise - Max. at 300A	39° C
Voltage - Maximum	15 kV
Voltage - Radio Interference	Ambient @ 9.41kV
Voltage Rating	15 kV
Withstand Current - Short Time (10 cycles)	12,000 Amps Asym.

### Logistics

Pallet Quantity	24 EA
Standard Package	1

### Product Assets

- [Catalogs - Type C-Porcelain Cutouts \(10A\)](#)
- [Installation Manuals - Load Break Cutout Installation Instructions](#)
- [Literature - SF11036E\\_HPS CHANCE RUS Cutout Listing](#)
- [Literature - Switching Line Card\\_FAQ\\_2019](#)
- [Sales Drawings - Cutout, LDBK, 15kV, 110 BIL \(SA730-1\)](#)
- [Technical Solutions - CH-C730133LD-SPEC-EN](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience \(VI10004E\)](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality \(VI10005E\)](#)



A proud member of the Hubbell Family.