



15/27 kV, 125 kV BIL, Type C Loadbreak Porcelain Cutout w/100A 12kAIC fuseholder

By Chance
Catalog # [C730213PX](#)

15/27 kV, 125 kV BIL, Loadbreak Type C Porcelain Cutout with a 100A, 12kAIC fuseholder, parallel-groove connector and an extended NEMA "B" crossarm bracket.



Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- Non Interchangeable Mounting Assembly

General

Bracket Type	Extended NEMA "B" for crossarm
Catalog Number	C730213PX
Description - Replacement	T730-213T
Fuse Holder Type	Cutout
UPC	096359463344

Dimensions

Weight	29.38 lb
--------	----------

Electrical Ratings

BIL	125 kV
Creep and Leakage Distance	12.6" (319mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A - removable buttonhead fuse link only
Reference Voltage Limit - Minimum	No Restrictions thru 14.9kV; *20.8 thru 24.9kV
Temperature Rise - Max. at 300A	40° C
Voltage - Radio Interference	36.2 micro-volts @ 15.66kV
Voltage Rating	15/27 kV

Logistics

Pallet Quantity	24 EA
Standard Package	1

Product Assets

- [Catalogs - Type C-Porcelain Cutouts](#)
- [Installation Manuals - Load Break Cutout Installation Instructions](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Literature - HUBBELL® | CHANCE® RUS CUTOUT LISTING](#)
- [Sales Drawings - Cutout, LDBK, 15/27 kV, 125 BIL](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality Experience](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CH-C730213PX-SPEC-EN | REV 6/2024