




# 15/27 kV, 125 kV BIL, Type C Linkbreak Porcelain Cutout / Arrester Combination w/100A 8kAIC fuseholder

By Chance  
Catalog # [C72DN211EX](#)



15/27 kV, 125 kV BIL, Linkbreak Type C Porcelain Cutout / Arrester Combination with a 100A, 8kAIC fuseholder, small eyebolt connector and an extended NEMA "B" crossarm bracket.

## Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- Ohio Brass Distribution Class Arresters in Standard, Heavy and Riser Pole Duty Ratings

## General

Bracket Type	Extended NEMA "B" for crossarm
Catalog Number	C72DN211EX
Description - Replacement	T720-211T
Fuse Holder Type	Cutout

## Electrical Ratings

BIL	125 kV
Creep and Leakage Distance	12.6" (319mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A
Reference Voltage Limit - Minimum	No Restrictions thru 14.9kV; *20.8 thru 24.9kV
Temperature Rise - Max. at 300A	33° C
Voltage - Radio Interference	Ambient @15.66kV
Voltage Rating	15/27 kV

## Logistics

Standard Package	1
------------------	---

## Product Assets

- [Catalogs - Type C-Porcelain Cutouts](#)
- [Literature - Switching Line Card\\_FAQ\\_2019](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
CH-C72DN211EX-SPEC-EN | REV 6/2024