



# 15/27 kV, 125 kV BIL, Type C Loadbreak Porcelain Cutout / Arrester Combination w/300A Solid Blade

By Chance  
Catalog # [C73EN233PX](#)



15/27 kV, 125 kV BIL, Loadbreak Type C Porcelain Cutout / Arrester Combination with a 300A solid blade, parallel-groove connector and an extended NEMA "B" crossarm bracket.

## Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- Ohio Brass Distribution Class Arresters in Standard, Heavy and Riser Pole Duty Ratings
- Non Interchangeable Mounting Assembly

## General

Bracket Type	Extended NEMA "B" for crossarm
Catalog Number	C73EN233PX
Description - Replacement	T730-233T
Fuse Holder Type	Cutout

## Electrical Ratings

BIL	125 kV
Creep and Leakage Distance	12.6" (319mm)
Current Rating	300 A
Reference Voltage Limit - Minimum	No Restrictions thru 14.9kV; *20.8 thru 24.9kV
Temperature Rise - Max. at 300A	40° C
Voltage - Radio Interference	36.2 micro-volts @ 15.66kV
Voltage Rating	15/27 kV
Withstand Current - Short Time (10 cycles)	12,000 Amps Asym.

## Logistics

Standard Package 1

## Product Assets

- [Catalogs - Type C-Porcelain Cutouts](#)
- [Literature - Switching Line Card\\_FAQ\\_2019](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
CH-C73EN233PX-SPEC-EN | REV 6/2024