



# 20/34.5 kV, 150 kV BIL, Type C Loadbreak Porcelain Cutout / Arrester Combination w/100A 12kAIC fuseholder

By CHANCE Utility  
Catalog # [C73EP313LB](#)



\*Representative Image

20/33.5 kV, 150 kV BIL, Loadbreak Type C Porcelain Cutout / Arrester Combination with a 100A, 12kAIC fuseholder, large eyebolt connector and a NEMA "B" crossarm bracket.

## Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- Ohio Brass Distribution Class Arresters in Standard, Heavy and Riser Pole Duty Ratings
- Non Interchangeable Mounting Assembly

## General

|                                       |                                  |
|---------------------------------------|----------------------------------|
| Bracket Type                          | NEMA "B" Heavy Duty for crossarm |
| Description - Replacement Fuse Holder | T730-313T                        |
| Type                                  | Cutout                           |

## Electrical Ratings

|                                   |  |
|-----------------------------------|--|
| BIL                               | 150 kV   |
| Creep and Leakage Distance        | 17.3" (440mm)                                    |
| Current Rating                    | 100 A  |
| Fuselink Current Range            | 1A to 100A - removable buttonhead fuse link only |
| Reference Voltage Limit - Minimum | No Restrictions thru 14.4kV; *20.8 thru 34.5kV   |
| Temperature Rise - Max. at 300A   | 40° C  |
| Voltage - Radio Interference      | 51.8 micro-volts @ 22kV                          |
| Voltage Rating                    | 20/33.5 kV                                       |

## Logistics

|                  |   |
|------------------|---|
| Standard Package | 1 |
|------------------|---|

## Product Assets

- [Catalogs - Type C-Porcelain Cutouts \(10A\)](#)
- [Literature - Switching Line Card\\_FAQ\\_2019](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience \(VI10004E\)](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality \(VI10005E\)](#)



A proud member of the Hubbell Family.