



## 20/34.5 kV, 150 kV BIL, Type C Loadbreak Porcelain Cutout / Arrester Combination w/100A 12kAIC fuseholder

By Chance  
Catalog # [C73EP313PD](#)



20/33.5 kV, 150 kV BIL, Loadbreak Type C Porcelain Cutout / Arrester Combination with a 100A, 12kAIC fuseholder, parallel-groove connector and a D-shape pole mounting bracket.

### Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- Ohio Brass Distribution Class Arresters in Standard, Heavy and Riser Pole Duty Ratings
- Non Interchangeable Mounting Assembly

### General

Bracket Type	D-shape for pole mounting
Catalog Number	C73EP313PD
Description - Replacement	T730-313T
Fuse Holder	
Type	Cutout

### Electrical Ratings

BIL	150 kV
Creep and Leakage Distance	17.3" (440mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A - removable buttonhead fuse link only
Reference Voltage Limit - Minimum	No Restrictions thru 14.4kV; *20.8 thru 34.5kV
Temperature Rise - Max. at 300A	40° C
Voltage - Radio Interference	51.8 micro-volts @ 22kV
Voltage Rating	20/33.5 kV

### Logistics

Standard Package 1

### Product Assets

- [Catalogs - Type C-Porcelain Cutouts](#)
- [Literature - Switching Line Card\\_FAQ\\_2019](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
CH-C73EP313PD-SPEC-EN | REV 6/2024