



15/27 kV, 125 kV BIL, Type C Loadbreak Porcelain Cutout / Arrester Combination w/100A 8kAIC fuseholder

By CHANCE Utility
Catalog # [C73DN211LB](#)



*Representative Image

15/27 kV, 125 kV BIL, Loadbreak Type C Porcelain Cutout / Arrester Combination with a 100A, 8kAIC fuseholder, large eyebolt connector and a NEMA "B" crossarm bracket.

Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- Ohio Brass Distribution Class Arresters in Standard, Heavy and Riser Pole Duty Ratings
- Non Interchangeable Mounting Assembly

General

| | |
|---------------------------------------|----------------------------------|
| Bracket Type | NEMA "B" Heavy Duty for crossarm |
| Description - Replacement Fuse Holder | T730-211T |
| Type | Cutout |

Electrical Ratings

| | |
|-----------------------------------|--|
| BIL | 125 kV |
| Creep and Leakage Distance | 12.6" (319mm) |
| Current Rating | 100 A |
| Fuselink Current Range | 1A to 100A |
| Reference Voltage Limit - Minimum | No Restrictions thru 14.9kV; *20.8 thru 24.9kV |
| Temperature Rise - Max. at 300A | 40° C |
| Voltage - Radio Interference | 36.2 micro-volts @ 15.66kV |
| Voltage Rating | 15/27 kV |

Logistics

| | |
|------------------|---|
| Standard Package | 1 |
|------------------|---|

Product Assets

- [Catalogs - Type C-Porcelain Cutouts \(10A\)](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience \(VI10004E\)](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality \(VI10005E\)](#)



A proud member of the Hubbell Family.