



15 kV, 110 kV BIL, Type C Standard Polymer Cutout w/100A 10kAIC fuseholder

By Chance
Catalog # CP710112PVM

15 kV, 110 kV BIL, Standard Type C Polymer Cutout with a 100A, 10kAIC fuseholder, parallel-groove connector and Easy On NEMA "B" crossarm bracket, Mechanical assist spring option.

Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- ESP (Enhanced Silicone Polymer) Insulating Material
- TDG (Thermal Diffusion Galvanization) Insulator Assembly Castings

General

| | |
|---------------------------|-------------------------------|
| Bracket Type | Easy On NEMA "B" for crossarm |
| Catalog Number | CP710112PVM |
| Corrosion Resistant? | No |
| Description - Replacement | T710-112TM |
| Fuse Holder | |
| Type | Cutout |
| UPC | 096359643586 |

Dimensions

| | |
|--------|-------|
| Weight | 11 lb |
|--------|-------|

Electrical Ratings

| | |
|-----------------------------------|------------------|
| BIL | 110 kV |
| Creep and Leakage Distance | 12.6" (319mm) |
| Current Rating | 100 A |
| Fuselink Current Range | 1A to 100A |
| Reference Voltage Limit - Minimum | Thru 14.4kV |
| Temperature Rise - Max. at 300A | 38° C |
| Voltage - Maximum | 15 kV |
| Voltage - Radio Interference | Ambient @ 9.41kV |
| Voltage Rating | 15 kV |



Logistics

| | |
|------------------|-------|
| Pallet Quantity | 63 EA |
| Standard Package | 1 |

Product Assets

- [Catalogs - Type C-Polymer Cutouts](#)
- [Installation Manuals - Standard Cutout Installation Instructions](#)
- [Literature - HUBBELL® | CHANCE® RUS CUTOUT LISTING](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Sales Drawings - 110KV BIL Polymer Cutout](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CH-CP710112PVM-SPEC-EN | REV 6/2024