



# 15 kV, 110 kV BIL, Type C Standard Polymer Cutout w/100A 16kAIC fuseholder

By CHANCE Utility  
Catalog # CP710114EZM

15 kV, 110 kV BIL, Standard Type C Polymer Cutout with a 100A, 16kAIC fuseholder, small eyebolt connector and no bracket.



\*Representative Image

## Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- ESP ( Enhanced Silicone Polymer ) Insulating Material
- TDG ( Thermal Diffusion Galvanization ) Insulator Assembly Castings

## General

Bracket Type	No Bracket
Description - Replacement Fuse Holder	T710-114TM
Type	Cutout

## Electrical Ratings

BIL	110 kV
Creep and Leakage Distance	12.6" (319mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A - removable buttonhead fuse link only
Reference Voltage Limit - Minimum	Thru 14.4kV
Temperature Rise - Max. at 300A	38° C
Voltage - Maximum	15 kV
Voltage - Radio Interference	Ambient @ 9.41kV
Voltage Rating	15 kV

## Logistics

Pallet Quantity	63 EA
Standard Package	1

## Product Assets

- [Catalogs - Type C-Polymer Cutouts \(10AA\)](#)
- [Installation Manuals - Standard Cutout Installation Instructions](#)
- [Literature - SF11036E\\_HPS CHANCE RUS Cutout Listing](#)
- [Literature - Switching Line Card\\_FAQ\\_2019](#)
- [Sales Drawings - 110KV BIL Polymer Cutout \(SAP710-1\)](#)
- [Technical Solutions - CH-CP710114EZM-SPEC-EN](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience \(VI10004E\)](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality \(VI10005E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CH-CP710114EZM-SPEC-EN | REV 1/2024